

HD2021T7 - HD2021T6



HD2021T7 - HD2021T6 DEBILITATING LUMINANCE AND LUMINANCE TRANSMITTERS

HD2021T7 - Transmitter for measuring EQUIVALENT VEILING LUMINANCE

The HD2021T7 probe allows converting the photometric quantity "equivalent veiling luminance" into a current (4...20 mA) or a voltage (0...10 V) signal according to the version chosen. If the acquisition station is far from the probe (>50 m), it is necessary to use the current output version.

In order to grant high accuracy, it is important to keep the surface of the outer lens clean. It is possible to wash them by using only water and standard papers for lens. The transmitter full scale can be chosen (when ordering) between two different values: 2000 cd/m² or 20000 cd/m². For orders of at least 5 pieces, it is possible to calibrate the scale to a value chosen by the customer.

The probe is used for the control of street lighting, in particular, the measurement of equivalent veiling luminance is essential to determine the threshold luminance at the entrance of the tunnels (UNI 11095:2011).

The measurement of debilitating luminance (L_v) consists of four components:

$$L_v = L_{seq} + L_{alm} + L_{par} + L_{cru}$$

where:

L_{seq} is the equivalent veiling luminance;

L_{alm} is the atmospheric luminance;

$L_{par} + L_{cru}$ is the luminance of the windshield and the dashboard ($=0.4 L_{seq}$).

The equivalent veiling luminance (L_{seq}) is measured according to standard UNI 11095: 2005 with the probe HD2021T7 as reported in the test report I.N.Ri.M. 08-1199-01. This quantity is measured and defined starting from the subtended angles greater than 1°.

The atmospheric luminance (L_{alm}) can be calculated from the table E2.2 of UNI 11095 (2011) standard or measured with the HD2021T7.2 probe.


The contribution of the luminance of the windshield (L_{par}) + the luminance of the dashboard (L_{cru}) is measured directly by inserting the HD2021T7 probe in a protective case. The window interface that separates the probe from the external environment simulates the behaviour of the windshield, so the value read by the probe in the container already includes this contribution.

INSTRUMENT TECHNICAL SPECIFICATIONS

Dimensions

(Length x Width x Height) 148 mm x 60 mm x 66 mm

Figure 1 - Dimensions of the HD2021T7 probe



SPECTRAL RESPONSE

The probe uses a silicon photodiode and a set of filters to correct the spectral response curve to make it equal to that of the human eye (photopic response). Figure 2 shows the trend of the relative spectral response according to the wavelength.

$f_1 < 9\%$ according to the standard photopic curve $V(\lambda)$.




Figure 2 - HD2021T7 Relative spectral response

ANGULAR RESPONSE

The equivalent veiling luminance (L_v) is estimated starting from the following formula:

$$L_v = 10 \sum_{\beta=1^\circ}^{\beta=90^\circ} \frac{L(\beta) \cdot \cos(\beta)}{\beta \cdot (\beta+1.5)} \cdot \Omega \quad \text{A}$$

where:

- $L(\beta)$ is the luminance of a source of disturbance measured at an angle β ,
- β is the angle between the pointing direction of the object to be watched and the source of interference,
- Ω is the solid angle

Figure 3 shows the sensitivity as a function of the angle of the probe. In the standard CIE88:2004 the equivalent veiling luminance is calculated by considering the contributions up to angles of 28.4°. By using Delta OHM probe HD2021T7 it is possible to evaluate contributions to greater angles (up to 40°).




Figure 3 - HD2021T7 Relative angular response

WORKING TEMPERATURE

The probe can work in a temperature range from -20° to +60° C. If the probe is placed in watertight containers, take care that there is no fogging or condensation on the window towards which the probe is overlooking. In this case the reading of the equivalent veiling luminance would be altered by systematic errors.

CALIBRATION

The calibration of the probe HD2021T7 is carried out by measuring the luminance on the output port of an integrating sphere with a known luminance. If requested, the uncertainty of the calibration of the probe with fixed full scale is 10% (confidence level of 95%).

TRANSMITTER INSTALLATION

The installation of the probe for the evaluation of the threshold luminance at the entrance of tunnels should be performed in compliance with the standard UNI 11095. The transmitter has IP52 protection degree.

In order to connect the transmitter, it is necessary to lift the lid (by unscrewing the four locking screws). For the 0...10 V version, please refer to Figure 4, while the version 4...20 mA is referred to Figure 5.




Figure 4 - Connection diagram for HD2021T... with voltage output




Figure 5 - Connection diagram for HD2021T... with current output

ORDERING CODES:

HD2021T7.xx: Transmitter for measuring the LUMINANCE of Equivalent Veiling, full scale according to the following table, power supply 16...40Vdc or 24 Vac. Amplified with output 4...20 mA or 0...10 Vdc according to the choice.

HD2021T7.2xx: Transmitter for measuring the LUMINANCE by a 2° angle, for the measurement of the atmospheric luminance L_{atm} , full scale according to the following table, power supply 16...40 Vdc or 24 Vac. Amplified with output 4...20 mA or 0...10 Vdc according to the choice.

	Output	Measurement range
HD2021T7.AV	0...10 V	0...2000 cd/m ²
HD2021T7.BV		0...20 kcd/m ²
HD2021T7.2.AV	4...20 mA	0...2000 cd/m ²
HD2021T7.AA		0...2000 cd/m ²
HD2021T7.BA		0...20 kcd/m ²
HD2021T7.2.AA		0...2000 cd/m ²

For a minimum order of 5 pcs, ranges upon request are available.

HD2021T6 - Transmitter for measuring LUMINANCE (cd/m²)

The probe HD2021T6 allows converting a photometric quantity Luminance (cd/m²) into a current (4...20 mA) or voltage (0...10 V) signal according to the version chosen. If the acquisition station is far from the probe (>50 m), the current version is required.

In order to ensure correct measurements, the outer surface of the lens must be kept clean. If necessary, clean the lens with water and lens cleaning paper. At the order time, it is possible to choose the transmitter sensitivity among three previously set values: 2 kcd/m², 20 kcd/m² or 200 kcd/m². For orders of quantities over 5 pieces, the full scale can be customized.

The probe is used for road lighting control. In particular, the measurement of luminance at a **20° angle (L₂₀)** is necessary to estimate threshold luminance at tunnel entrances (CIE standard 88:2004. This standard foresees the measurement of debilitating luminance in future).

Moreover, the probe can be used for calculating vertical illuminance (E_v) as prescribed in the above-mentioned standard.

Finally, the probe can be used for any application where the measurement of luminance is required, for example projector screens, diaphanoscopes etc.

INSTRUMENT TECHNICAL SPECIFICATIONS

Dimensions

(Length x Width x Height) 148.5 mm x 60 mm x 66 mm




Figure 6 - HD2021T6 probe dimensions

SPECTRAL RESPONSE

The probe is equipped with a silicon photodiode and a series of filters to correct the spectral response curve and make it equal to that of the human eye (photopic response). Figure 7 shows the trend of the relative spectral response depending on the wavelength.

f'1 <9% according to the standard photopic curve V(λ).




Figure 7 - HD2021T6 probe relative spectral response

FIELD OF VIEW

The total field of view of HD2021T6 probe is 20°.

WORKING TEMPERATURE

The probe can work in a temperature range from -20° to +60° C. If the probe is placed in watertight containers, take care that there is no fogging or condensation on the window towards which the probe is overlooking. In this case the reading of the equivalent veiling luminance would be altered by systematic errors.

CALIBRATION

The calibration of the probe HD2021T6 is carried out by measuring the luminance on the output port of an integrating sphere with a known luminance. If requested, the uncertainty of the calibration of the probe with fixed full scale is 5% (confidence level of 95%).

TRANSMITTER INSTALLATION

The installation of the probe for the evaluation of the threshold luminance at the entrance to the galleries has to be performed according to standard CIE 88:2004. The transmitter has IP52 protection degree.

In order to connect the transmitter, it is necessary to lift the lid (by unscrewing the four locking screws). For the 0...10 V version refer to Figure 4, while for the version 4...20 mA refer to Figure 5 of HD2021T7.

ORDERING CODES

HD2021T6.xx: Transmitter for measuring the LUMINANCE, full scale according to the following table, power supply 16...40 Vdc or 24 Vac. Amplified with output 4...20 mA or 0...10 Vdc according to the choice.

Model	Output	Measurement range
HD2021T6.AV	0...10 V	0...2000 cd/m ²
HD2021T6.BV		0...20 kcd/m ²
HD2021T6.CV		0...200 kcd/m ²
HD2021T6.AA	4...20 mA	0...2000 cd/m ²
HD2021T6.BA		0...20 kcd/m ²
HD2021T6.CA		0...200 kcd/m ²

For a minimum order of 5 pcs, ranges upon request are available.

WARRANTY

The manufacturer is required to respond to the “factory warranty” only in those cases provided by Legislative Decree 6 September 2005 - n. 206. Each instrument is sold after rigorous inspections; if any manufacturing defect is found, it is necessary to contact the distributor where the instrument was purchased from. During the warranty period (24 months from the date of invoice) any manufacturing defects found will be repaired free of charge. Misuse, wear, neglect, lack or inefficient maintenance as well as theft and damage during transport are excluded. Warranty does not apply if changes, tampering or unauthorized repairs are made on the product. Solutions, probes, electrodes and microphones are not guaranteed as the improper use, even for a few minutes, may cause irreparable damages. The manufacturer repairs the products that show defects of construction in accordance with the terms and conditions of warranty included in the manual of the product. For any dispute, the competent court is the Court of Padua. The Italian law and the “Convention on Contracts for the International Sales of Goods” apply

TECHNICAL INFORMATION

The quality level of our instruments is the result of the continuous product development. This may lead to differences between the information reported in the manual and the instrument you have purchased. We reserves the right to change technical specifications and dimensions to fit the product requirements without prior notice.

DISPOSAL INFORMATION



Electrical and electronic equipment marked with specific symbol in compliance with 2012/19/EU Directive must be disposed of separately from household waste. European users can hand them over to the dealer or to the manufacturer when purchasing a new electrical and electronic equipment, or to a WEEE collection point designated by local authorities. Illegal disposal is punished by law.

Disposing of electrical and electronic equipment separately from normal waste helps to preserve natural resources and allows materials to be recycled in an environmentally friendly way without risks to human health.

